

Han CGM-P M32x1,5 D.18-25mm grey



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5196
Specification	Han CGM-P M32x1,5 D.18-25mm grey
HARTING eCatalogue	https://harting.com/19000005196

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-P
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤6.5 Nm (depending on the cable and the seal insert used)
Wrench size	42
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M32
Clamping range	18 ... 25 mm
Width across corners	46.8 mm

Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 7035 (light grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

UL / CSA	UL 514B QCRV.E479780
	CSA-C22.2 No. 18.3 QCRV7.E479780
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	3.84 g
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140123953
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431