

Cable Seal plastic M25x1.5 6,5-9,5mm



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 12 000 5156 |
| Specification | Cable Seal plastic M25x1.5 6,5-9,5mm |
| HARTING eCatalogue | https://harting.com/19120005156 |

Identification

| | |
|------------------------------|---|
| Category | Accessories |
| Series of hoods/housings | Han-Compact® |
| Type of accessory | Cable gland |
| Description of the accessory | for hoods for cable to cable housing |

Technical characteristics

| | |
|--|---|
| Tightening torque | ≤6 Nm (depending on the cable and the seal insert used) |
| Wrench size | 30 |
| Limiting temperature | -40 ... +100 °C |
| Degree of protection acc. to IEC 60529 | IP65 |
| Size | M25 |
| Clamping range | 6.5 ... 9.5 mm |

Material properties

| | |
|-----------------------------|---------------|
| Material (cable glands) | Thermoplastic |
| Colour (cable gland) | Black |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |

Material properties

| | |
|--------------------------------------|---|
| REACH SVHC substances | 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326) |
| California Proposition 65 substances | Not contained |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 8 g |
| Country of origin | Germany |
| European customs tariff number | 39174000 |
| GTIN | 5713140124059 |
| eCl@ss | 27140807 Additional components cable gland |
| ETIM | EC003608 |
| UNSPSC 24.0 | 39121431 |