

R 15-GG mit M16



Image is for illustration purposes only. Please refer to product description.

Part number	19 15 000 0401
Specification	R 15-GG mit M16
HARTING eCatalogue	https://harting.com/19150000401

Identification

Category	Hoods / Housings
Series	R 15
Type of hood/housing	Hood

Version

Number of cable entries	1
Cable entry	1x M16
Locking type	Screw locking

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polycarbonate (PC)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)



Pushing Performance
Since 1945

Material properties

Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	10
Net weight	16.28 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140124325
eCl@ss	27440224 Shell for circular connectors
ETIM	EC003556
UNSPSC 24.0	39121405