

Han 3A-HTE plastic (9-17mm)



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods / Housings
Series of hoods/housings	Han A®
Type of hood/housing	Hood
Description of hood/housing	With integrated cable gland

Version

Size	3 A
Version	Top entry
Number of cable entries	1
Cable entry	1x Integrated
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4 4X 12

Technical characteristics

Cable diameter	9 ... 17 mm
----------------	-------------

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	10
Net weight	17.5 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140124370
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466