

## Han 16HP Direct/B-HTE-M40



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 39 616 0448                                                                |
| Specification      | Han 16HP Direct/B-HTE-M40                                                     |
| HARTING eCatalogue | <a href="https://harting.com/19396160448">https://harting.com/19396160448</a> |

### Identification

|                          |                              |
|--------------------------|------------------------------|
| Category                 | Hoods / Housings             |
| Series of hoods/housings | Han <sup>®</sup> HP Direct B |
| Type of hood/housing     | Hood                         |

### Version

|                         |               |
|-------------------------|---------------|
| Size                    | 16 B          |
| Version                 | Top entry     |
| Number of cable entries | 1             |
| Cable entry             | 1x M40        |
| Locking type            | Screw locking |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Tightening torque (screw locking)      | 4 Nm                                           |
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP66<br>IP68<br>IP69 / IPX9K acc. to ISO 20653 |

### Material properties

|                         |                      |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast   |
| Surface (hood/housing)  | Powder-coated        |
| Colour (hood/housing)   | RAL 7037 (dust grey) |
| Material (seal)         | NBR                  |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Material (locking)                   | Stainless steel                     |
| RoHS                                 | compliant                           |
| ELV status                           | compliant                           |
| China RoHS                           | e                                   |
| REACH Annex XVII substances          | Not contained                       |
| REACH ANNEX XIV substances           | Not contained                       |
| REACH SVHC substances                | Not contained                       |
| California Proposition 65 substances | Yes                                 |
| California Proposition 65 substances | Nickel<br>Naphthalene               |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels   | R1 (HL 1-3)<br>R7 (HL 1-3)          |

## Specifications and approvals

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
| Approvals      | CE                       |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 328 g                                    |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140182462                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |