

Han 48HPR mounting cover 2xM50 1xM20



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 048 9813
Specification	Han 48HPR mounting cover 2xM50 1xM20
HARTING eCatalogue	https://harting.com/19400489813

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Mounting cover
Description of hood/housing	Distance bolt M6

Version

Size	48 B
Number of cable entries	3
Cable entry	2x M50 1x M20
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	4 distance pieces 4x M6 screw 4 washers

Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	618.35 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140130395
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467