



Pushing Performance
Since 1945

Han 34HPR EasyCon cover 4xM40



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 134 9943
Specification	Han 34HPR EasyCon cover 4xM40
HARTING eCatalogue	https://harting.com/19401349943

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR EasyCon
Type of hood/housing	Mounting cover
Description of hood/housing	for surface mounted housings for hoods

Version

Size	34 HPR
Number of cable entries	4
Cable entry	4x M40
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Tightening torque	6 Nm Mounting cover 6 Nm Distance bolt
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
-------------------------	---



Pushing Performance
Since 1945

Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Commercial data

Packaging size	1
Net weight	495 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140175488
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466