

## Han-Eco 16B-HSM1-for DL-M32 with cover



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 43 016 0227                                                                |
| Specification      | Han-Eco 16B-HSM1-for DL-M32 with cover                                        |
| HARTING eCatalogue | <a href="https://harting.com/19430160227">https://harting.com/19430160227</a> |

### Identification

|                             |                           |
|-----------------------------|---------------------------|
| Category                    | Hoods / Housings          |
| Series of hoods/housings    | Han-Eco <sup>®</sup> B    |
| Type of hood/housing        | Surface mounted housing   |
| Description of hood/housing | With thermo-plastic cover |

### Version

|                         |                                    |
|-------------------------|------------------------------------|
| Size                    | 16 B                               |
| Version                 | Side entry                         |
| Number of cable entries | 1                                  |
| Cable entry             | 1x M32                             |
| Locking type            | Double locking lever (on the hood) |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Number of relockings                   | ≥500                                           |
| Degree of protection acc. to IEC 60529 | IP66                                           |

### Material properties

|                         |                                          |
|-------------------------|------------------------------------------|
| Material (hood/housing) | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)   | RAL 9005 (jet black)                     |
| Material (seal)         | NBR                                      |



**Pushing Performance**  
Since 1945

## Material properties

|                                           |                              |
|-------------------------------------------|------------------------------|
| Colour (seal)                             | RAL 9005 (jet black)         |
| Material flammability class acc. to UL 94 | V-0                          |
| RoHS                                      | compliant                    |
| ELV status                                | compliant                    |
| China RoHS                                | e                            |
| REACH Annex XVII substances               | Not contained                |
| REACH ANNEX XIV substances                | Not contained                |
| REACH SVHC substances                     | Not contained                |
| California Proposition 65 substances      | Not contained                |
| Fire protection on railway vehicles       | EN 45545-2 (2020-08)         |
| Requirement set with Hazard Levels        | R22 (HL 1-2)<br>R23 (HL 1-3) |

## Specifications and approvals

|                |                                                             |
|----------------|-------------------------------------------------------------|
| Specifications | IEC 61984<br>EN 45545-2 Fire protection on railway vehicles |
| Approvals      | CE                                                          |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 242.45 g                                 |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140179288                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |