

Han-INOX 10B-HBM-SL-hinged cover



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 310 0303
Specification	Han-INOX 10B-HBM-SL-hinged cover
HARTING eCatalogue	https://harting.com/19443100303

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With metal cover

Version

Size	10 B
Locking type	Single locking lever
Field of application	Hoods/housings for harsh environments

Technical characteristics

Tightening torque (fixing screw)	1 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	FPM



Pushing Performance
Since 1945

Material properties

Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	516.5 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132061
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466