

Han 3 EMC HOOD ANGLED ENTRY 2PEGS M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 003 1640
Specification	Han 3 EMC HOOD ANGLED ENTRY 2PEGS M20
HARTING eCatalogue	https://harting.com/19620031640

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] EMC
Type of hood/housing	Hood

Version

Size	3 A
Version	Side entry
Number of cable entries	1
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated



Pushing Performance
 Since 1945

Material properties

Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	10
Net weight	75 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132368
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466