

## Han 6EMC/B-HTE-HC-for SL-M32-HMC



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 206 0447
Specification	Han 6EMC/B-HTE-HC-for SL-M32-HMC
HARTING eCatalogue	<a href="https://b2b.harting.com/19622060447">https://b2b.harting.com/19622060447</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> EMC/B
Type of hood/housing	Hood

### Version

Size	6 B
Version	Top entry
Number of cable entries	1
Cable entry	1x M32
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥10,000
Note on the mating cycles	Mating cycles with other HMC components
Degree of protection acc. to IEC 60529	IP65 IP66
Type rating acc. to UL 50 / UL 50E	4 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated



Pushing Performance  
Since 1945

Material properties

Colour (hood/housing)	Unpainted
-----------------------	-----------

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	128.4 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140171534
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors