



Pushing Performance
Since 1945

Han 10EMC/B-HTE-M32 (HT)



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 810 0427
Specification	Han 10EMC/B-HTE-M32 (HT)
HARTING eCatalogue	https://harting.com/19628100427

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® EMC/B
	Han® High Temp
Type of hood/housing	Hood
Type	High construction

Version

Size	10 B
Version	Top entry
Number of cable entries	1
Cable entry	1x M32
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
	-40 ... +200 °C With Han® High Temp components
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	IP66
Type rating acc. to UL 50 / UL 50E	4
	12



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	130 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132702
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466