



Pushing Performance
Since 1945

LC connector multimode 3mm



Image is for illustration purposes only. Please refer to product description.

Part number	20 10 125 8211
Specification	LC connector multimode 3mm
HARTING eCatalogue	https://harting.com/20101258211

Identification

Category	Contacts
Series	LC
Type of contact	FO contact
Description of the contact	for multimode
Features	for cable diameter up to 3 mm

Version

Manufacturing process	Turned contacts
-----------------------	-----------------

Technical characteristics

Limiting temperature	-40 ... +75 °C
----------------------	----------------

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
	Naphthalene

Commercial data

Packaging size	2
Net weight	3.5 g
Country of origin	Germany
European customs tariff number	85367000
GTIN	5713140133624
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522