

M12 wall bracket / gender changer



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 000 0036
Specification	M12 wall bracket / gender changer
HARTING eCatalogue	https://b2b.harting.com/21010000036

Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	Panel mounting parts

Technical characteristics

Limiting temperature	-40 ... +85 °C
----------------------	----------------

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (accessories)	Thermoplastic
Colour (accessories)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521
----------	--



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	7.85 g
Country of origin	Taiwan
European customs tariff number	85389099
GTIN	5713140136533
ETIM	EC002943
eCl@ss	27440292 Connector component (accessories)