

M12 housing female frontmounting packed



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 301 2003
Specification	M12 housing female frontmounting packed
HARTING eCatalogue	https://harting.com/21033012003

Identification

Category	Accessories
Series	Circular connectors M12
Identification	PushPull
Type of accessory	Housing
Description of the accessory	for front mounting

Version

Gender	Female
Locking type	Screw locking PushPull

Technical characteristics

Tightening torque	2 Nm Lock nut
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

PROFINET	Yes
----------	-----

Commercial data

Packaging size	10
Net weight	16 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140137547
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400