

M12-ADPT-M12/M12-5/5P-ACOD-M/F/F-STR



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 321 9400
Specification	M12-ADPT-M12/M12-5/5P-ACOD-M/F/F-STR
HARTING eCatalogue	https://harting.com/21033219400

Identification

Category	Accessories
Series	Circular connectors M12
Connector 1	Female
	5 poles
	A-coding
Connector 2	Female
	5 poles
	A-coding
Type of accessory	Y-distributor

Version

Gender	Male
	Female
Shielding	Unshielded
Number of contacts	5
Coding	A-coding

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Limiting temperature	-25 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP67 mated condition



Pushing Performance
 Since 1945

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Thermoplastic polyurethane (TPU)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

Commercial data

Packaging size	1
Net weight	29 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140236646
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400



Pushing Performance
Since 1945

Pin assignment

