

## M17 Crimp Contact 1,0mm,male,1,5mm²



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 21 17 071 0000                                                                |
| Specification      | M17 Crimp Contact 1,0mm,male,1,5mm²                                           |
| HARTING eCatalogue | <a href="https://harting.com/21170710000">https://harting.com/21170710000</a> |

### Identification

|                 |                         |
|-----------------|-------------------------|
| Category        | Contacts                |
| Series          | Circular connectors M17 |
| Type of contact | Crimp contact           |

### Version

|                       |                   |
|-----------------------|-------------------|
| Termination method    | Crimp termination |
| Gender                | Male              |
| Manufacturing process | Turned contacts   |

### Technical characteristics

|                               |                   |
|-------------------------------|-------------------|
| Conductor cross-section       | 1 ... 1.5 mm²     |
| Conductor cross-section [AWG] | AWG 18 ... AWG 16 |
| Stripping length              | 5 mm              |
| Limiting temperature          | -40 ... +125 °C   |

### Material properties

|                             |               |
|-----------------------------|---------------|
| Material (contacts)         | Copper alloy  |
| Surface (contacts)          | Gold plated   |
| RoHS                        | compliant     |
| ELV status                  | compliant     |
| China RoHS                  | e             |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances  | Not contained |



Pushing Performance  
Since 1945

Material properties

|                       |               |
|-----------------------|---------------|
| REACH SVHC substances | Not contained |
|-----------------------|---------------|

Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 100                                        |
| Net weight                     | 0.3 g                                      |
| Country of origin              | Romania                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140819733                              |
| eCl@ss                         | 27440204 Contact for industrial connectors |
| ETIM                           | EC000796                                   |
| UNSPSC 24.0                    | 39121522                                   |