



Pushing Performance  
Since 1945

# M17-INS-SIG-CRT-17P-FE



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 506 0000
Specification	M17-INS-SIG-CRT-17P-FE
HARTING eCatalogue	<a href="https://harting.com/21175060000">https://harting.com/21175060000</a>

## Identification

Category	Inserts
Series	Circular connectors M17
Identification	Signal
Element	Inserts

## Version

Termination method	Crimp termination
Gender	Female
Number of contacts	17
Number of signal contacts	17

## Technical characteristics

Rated current	3.6 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

Specifications	IEC 61984
	IEC 60664-1
UL / CSA	UL 2237 / 2238 in preparation
Approvals	CE

## Commercial data

Packaging size	1
Net weight	2.7 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140819504
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421