

## M5 3-pol st/- m/- PUR 2.0M



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 21 34 030 0312 020                                                                  |
| Specification      | M5 3-pol st/- m/- PUR 2.0M                                                          |
| HARTING eCatalogue | <a href="https://harting.com/21340300312020">https://harting.com/21340300312020</a> |

### Identification

|               |                              |
|---------------|------------------------------|
| Category      | System cabling               |
| Series        | Circular connectors M5       |
| Element       | Cable assemblies             |
| Specification | Pre-assembled on one side    |
| Connector 1   | M5 A-coding<br>Male Straight |
| Type of cable | Copper cable (round)         |

### Version

|                 |                         |
|-----------------|-------------------------|
| Cable length    | 2 m                     |
| Number of cores | 3                       |
| Core structure  | 3x 0.25 mm <sup>2</sup> |
| Coding          | A-coding                |

### Technical characteristics

|                      |                |
|----------------------|----------------|
| Limiting temperature | -25 ... +80 °C |
|----------------------|----------------|

### Material properties

|                  |                                                        |
|------------------|--------------------------------------------------------|
| Material (cable) | PUR (polyurethane)                                     |
| Colour (cable)   | Black                                                  |
| RoHS             | compliant with exemption                               |
| RoHS exemptions  | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status       | compliant with exemption                               |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| China RoHS                           | 50                                   |
| REACH Annex XVII substances          | Not contained                        |
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | 567c8b78-5fa0-43aa-a4c0-beb9d99b7769 |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead<br>Nickel                       |

## Specifications and approvals

|           |    |
|-----------|----|
| Approvals | CE |
|-----------|----|

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 1                                       |
| Country of origin              | Germany                                 |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140283404                           |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |
| ETIM                           | EC001855                                |
| UNSPSC 24.0                    | 26121604                                |