

## M5 A-cod 4-pol st/- f/- PUR 2.0M



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 040 0413 020
Specification	M5 A-cod 4-pol st/- f/- PUR 2.0M
HARTING eCatalogue	<a href="https://harting.com/21340400413020">https://harting.com/21340400413020</a>

### Identification

Category	System cabling
Series	Circular connectors M5
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M5 A-coding Female Straight
Type of cable	Copper cable (round)

### Version

Cable length	2 m
Number of cores	4
Core structure	4x 0.25 mm <sup>2</sup>
Coding	A-coding

### Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

### Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Net weight	57.5 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140283442
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604