



Pushing Performance
Since 1945

M12 Y-cod 8-pol st/st m/f PUR 10m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 262 7840 100
Specification	M12 Y-cod 8-pol st/st m/f PUR 10m
HARTING eCatalogue	https://harting.com/21342627840100

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 Y-coding Male Straight
Connector 2	M12 Y-coding Female Straight
Type of cable	Copper cable (round)

Version

Cable length	10 m
Number of cores	8
Core structure	4x AWG20 + 1x 4x AWG26
Coding	Y-coding

Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green



Pushing Performance
Since 1945

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	1,000 g
Country of origin	Germany
European customs tariff number	85444995
GTIN	5713140282568
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600