

M12 Cable Assembly D-cod st/st m/m 10,0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 929 2477 100
Specification	M12 Cable Assembly D-cod st/st m/m 10,0m
HARTING eCatalogue	https://harting.com/21349292477100

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight
Connector 2	M12 D-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	10 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-25 ... +70 °C

Material properties

Material (cable)	PUR (polyurethane)
------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (cable)	Green
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
Approvals	CE
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	669 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140145269
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600