

## M23\_12P MA,Int-thread,ANG PVC cable,10M



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 340 0C71 100
Specification	M23_12P MA,Int-thread,ANG PVC cable,10M
HARTING eCatalogue	<a href="https://harting.com/21373400C71100">https://harting.com/21373400C71100</a>

### Identification

Category	System cabling
Series	Circular connectors M23
Identification	Signal
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M23 Male Angled
Type of cable	Copper cable (round)
Features	Flame retardancy Oil and UV resistant Highly EMC resistant

### Version

Cable length	10 m
Number of cores	12
Core structure	12x AWG 18

### Technical characteristics

Rated current	6 A
Rated voltage	300 V
Limiting temperature	-40 ... +80 °C
Degree of protection acc. to IEC 60529	IP67

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (cable)	PVC
Colour (cable)	Black
Material (overmoulding)	Thermoplastic polyurethane (TPU)
Colour (overmoulding)	Black

## Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140241015
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line