

M23_19P FE,Int-thread,STR PVC cable,10M



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 350 0D75 100
Specification	M23_19P FE,Int-thread,STR PVC cable,10M
HARTING eCatalogue	https://harting.com/21373500D75100

Identification

Category	System cabling
Series	Circular connectors M23
Identification	Signal
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M23 Female Straight
Type of cable	Copper cable (round)
Features	Flame retardancy Oil and UV resistant Highly EMC resistant

Version

Cable length	10 m
Number of cores	19
Core structure	3x AWG 18 + 16x AWG 22

Technical characteristics

Rated voltage	150 V
Rated current (signal)	2 A
Rated current (power)	9 A
Limiting temperature	-40 ... +80 °C
Degree of protection acc. to IEC 60529	IP67



Pushing Performance
Since 1945

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (cable)	PVC
Colour (cable)	Black
Material (overmoulding)	Thermoplastic polyurethane (TPU)
Colour (overmoulding)	Black

Commercial data

Packaging size	1
Net weight	1,940 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140241213
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line