

M17 MA str molded 6+PE PUR open end,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 510 0701 050
Specification	M17 MA str molded 6+PE PUR open end,5m
HARTING eCatalogue	https://harting.com/21375100701050

Identification

Category	System cabling
Series	Circular connectors M17
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M17 Overmoulded Male Straight
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	7
Core structure	6x 0.5 mm ² + 1 mm ²

Technical characteristics

Rated current	8 A
Rated voltage	300 V
Limiting temperature	-20 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140240704
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604