

## M12 A-cod 5-pol st/- m/- PUR PP 1.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 200 0552 010
Specification	M12 A-cod 5-pol st/- m/- PUR PP 1.0m
HARTING eCatalogue	<a href="https://harting.com/21402000552010">https://harting.com/21402000552010</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Male Straight
Type of cable	Copper cable (round)

### Version

Cable length	1 m
Number of cores	5
Core structure	5x 0.34 mm <sup>2</sup>
Shielding	Shielded
Number of contacts	5
Coding	A-coding
Locking type	PushPull

### Technical characteristics

Rated voltage	48 V AC 60 V DC
Limiting temperature	-50 ... +80 °C moved -30 ... +80 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.7 mm ± 0.2 mm



**Pushing Performance**  
Since 1945

## Technical characteristics

Minimum bending radius	5x Cable diameter (singular bending)
	10x Cable diameter (repeated bending)

## Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black

## Commercial data

Packaging size	1
Net weight	72 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140491076
eCl@ss	27060311 Assembled sensor actuator-line
UNSPSC 24.0	26121604