

M12-ADPT-M12/M12-5/4P-ACOD-M/F/F-STR



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 21 43 311 9500 |
| Specification | M12-ADPT-M12/M12-5/4P-ACOD-M/F/F-STR |
| HARTING eCatalogue | https://harting.com/21433119500 |

Identification

| | |
|-------------------|-------------------------|
| Category | Accessories |
| Series | Circular connectors M12 |
| Connector 1 | Male |
| Connector 2 | Female |
| Type of accessory | T-splitter |

Version

| | |
|--------------------|------------|
| Gender | Male |
| | Female |
| Shielding | Unshielded |
| Number of contacts | 4 |
| | 5 |
| Coding | A-coding |

Technical characteristics

| | |
|--|----------------|
| Rated current | 4 A |
| Rated voltage | 60 V AC/DC |
| Rated impulse voltage | 1.5 kV |
| Limiting temperature | -25 ... +85 °C |
| Mating cycles | ≥100 |
| Degree of protection acc. to IEC 60529 | IP67 |

Material properties

| | |
|---------------------|--------------|
| Material (contacts) | Copper alloy |
|---------------------|--------------|



Pushing Performance
Since 1945

Material properties

Surface (contacts) Au over Ni Mating side

Material flammability class acc. to UL 94 V-0

Specifications and approvals

Specifications IEC 61076-2-101

Commercial data

Packaging size 1

Country of origin Germany

European customs tariff number 85366990

GTIN 5713140236653

eCl@ss 27440292 Connector component (accessories)

ETIM EC002943

UNSPSC 24.0 39121400