



Pushing Performance
Since 1945

ix Type A OM Profinet B PVC 1.0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 313 1409 010
Specification	ix Type A OM Profinet B PVC 1.0m
HARTING eCatalogue	https://harting.com/33483131409010

Identification

Category	System cabling
Series	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® PushPull IP20
	Type A
	Overmoulded
	IDC termination
Connector 2	HARTING ix Industrial® PushPull IP20
	Type A
	Overmoulded
	IDC termination
Type of cable	Copper cable (round)

Version

Cable length	1 m
Number of cores	4
Core structure	4x AWG 22/7
Number of contacts	10

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-30 ... +70 °C unmoved
	-20 ... +60 °C moved

Material properties

Material (cable)	PVC
Colour (cable)	Green
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
	UN/ECE-R 118 fire protection for rolling stock
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	82.5 g
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140330313
eCl@ss	27061801 Data and communication cable (copper)