

Single Frame, Ni plated, plastic cover



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 000 0100
Specification	Single Frame, Ni plated, plastic cover
HARTING eCatalogue	https://harting.com/39500000100

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Frames
Specification	Single Metal version, nickel plated (electrically conductive) Transparent plastic cover

Technical characteristics

Limiting temperature	-10 ... +60 °C
Storage temperature	-25 ... +60 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Smoothed surface
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)



Pushing Performance
Since 1945

Material properties

Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	1
Net weight	210.37 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140154759
eCl@ss	27182810 Cover/infill panel/identification strip (electrical cabinet)
ETIM	EC002617
UNSPSC 24.0	39121321