

Double Frame, Ni plated, metal cover



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 000 0210
Specification	Double Frame, Ni plated, metal cover
HARTING eCatalogue	https://harting.com/39500000210

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Frames
Specification	 Double Metal version, nickel plated (electrically conductive) Metal cover, nickel plated

Technical characteristics

Limiting temperature	-10 ... +60 °C
Storage temperature	-25 ... +60 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Smoothed surface
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
----------------	---

Commercial data

Net weight	0.5 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140154797
eCl@ss	27182810 Cover/infill panel/identification strip (electrical cabinet)
ETIM	EC002617
UNSPSC 24.0	39121321