

Data module (RJ45;SUB-D9,f-f;SUB-D9,m-m)



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 003 0111
Specification	Data module (RJ45;SUB-D9,f-f;SUB-D9,m-m)
HARTING eCatalogue	https://b2b.harting.com/39500030111

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Data connectors
Specification	Without shielding plate
	RJ45 female/female gender changer, 8-pin, metal, Cat. 5e
	D-Sub 1 (9 poles) female/female gender changer
	D-Sub 1 (9 poles) male/male gender changer

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 508 NRAQ2.E253944
	CSA-C22.2 No. 142 NRAQ8.E253944

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	67 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140155121
ETIM	EC002620
eCl@ss	27182890 Elements for switching cabinet, housing, rack (unspecified)