

InduCom 9p 1T-entry kn-screw 4-40



Image is for illustration purposes only. Please refer to product description.

Part number	61 03 001 0010 160
Specification	InduCom 9p 1T-entry kn-screw 4-40
HARTING eCatalogue	https://harting.com/61030010010160

Identification

Category	Hoods / Housings
Series of hoods/housings	D-Sub InduCom
Type of hood/housing	Shell housing
Description of hood/housing	With internal earth

Version

Size	D-Sub 1
Number of cable entries	1
Cable entry	1x
Strain relief	An additional InduCom cable clamp or a crimp flange - ferrule combination is available dependant on the use of the cable.
Locking type	Knurled screw Thread 4-40 UNC
ground connection	With internal grounding block
2 parts	Yes
Separable	Yes

Technical characteristics

Tightening torque	0.4 Nm ground connection
	0.4 Nm cover screw
	0.4 Nm Locking screw
Limiting temperature	-55 ... +125 °C
Degree of protection acc. to IEC 60529	IP30



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Zinc die-cast
Material (screw)	Steel, nickel plated
Length	38.6 mm
Width	31 mm
Height	14.8 mm

Commercial data

Packaging size	10
Net weight	40 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140222557
ETIM	EC001133
eCl@ss	27440213 D-Sub hood