



Pushing Performance
Since 1945

Ha-EIZ4 EIZ4-2.0M/KETH



Image is for illustration purposes only. Please refer to product description.

Part number	72 MD M4M DM40 20K
Specification	Ha-EIZ4 EIZ4-2.0M/KETH
HARTING eCatalogue	https://harting.com/72MDM4MDM4020K

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight
Connector 2	M12 D-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	2 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-35 ... +80 °C

Material properties

Material (cable)	PVC
------------------	-----



Pushing Performance
Since 1945

Material properties

Colour (cable) Green

Specifications and approvals

Approvals	CE
PROFINET	Yes

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140247291
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600