

Ha-MK4 MZ4-2M



Image is for illustration purposes only. Please refer to product description.

Part number	72 MN F4M NM40 20
Specification	Ha-MK4 MZ4-2M
HARTING eCatalogue	https://harting.com/72MNF4MNM4020

Identification

Category	System cabling
Series	Circular connectors 7/8"
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	7/8" Male Straight
Connector 2	7/8" Female Straight
Type of cable	Copper cable (round)

Version

Cable length	2 m
Number of cores	4
Core structure	4x AWG 16

Technical characteristics

Limiting temperature	-35 ... +75 °C
----------------------	----------------

Material properties

Material (cable)	PVC
Colour (cable)	Black



Pushing Performance
Since 1945

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	350 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140261785
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)