



Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	1/0 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1.0 in.
Stud Size	1/4 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	N/A
Panduit Color Code on Barrel	PINK
Panduit Die Index No. on Barrel	P42
Alternate Industry Die Index No. () on Barrel	(12)



- Color coded barrel markings



						<div><div><div>PANDUIT</div><div>CORP. TINLEY PARK, ILLINOIS</div></div><div>LCAN1/0-14H-X Copper Lug - One-Hole, Narrow Tongue, Standard Barrel, 45° Angle Tongue</div></div>		
00	5/18	JHNU	JHNU	DRAWING RELEASED	043942			
REV	DATE	BY	CHK	DESCRIPTION	ECN		SCALE N/A	DRAWING NO / CAD FILE LCAN1_0-14H-CUST