

BMKL 15X 9 WH - Label sheet, DIN A4



0803663

<https://www.phoenixcontact.com/us/products/0803663>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label sheet, DIN A4, Sheet, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, Number of individual labels: 290, text field height: 9 mm, text field width: 15 mm



Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking"
- The unperforated SK-U... sheets are available for custom label designs

Commercial data

Item number	0803663
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG13
Product key	BG2414
Catalog page	Page 344 (C-3-2019)
GTIN	4017918007621
Weight per piece (including packing)	14.68 g
Weight per piece (excluding packing)	14.28 g
Customs tariff number	39199080
Country of origin	DE

Technical data

Product properties

Product type	Device marking
--------------	----------------

Marking

Number of individual labels	290
Number of individual labels per row	10
Identification technology	Office laser printing

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 200 °C (230 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

BMKL 15X 9 WH - Label sheet, DIN A4



0803663

<https://www.phoenixcontact.com/us/products/0803663>

Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2


Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Recommended ambient temperature (storage/transport)	20 °C ... 25 °C
Recommended humidity (storage/transport)	40 % ... 50 %
Shelf life	2 years

Dimensions

Dimensional drawing	
Width	15 mm
Length	9 mm

Text field

BMKL 15X 9 WH - Label sheet, DIN A4



0803663

<https://www.phoenixcontact.com/us/products/0803663>

Text field width	15 mm
Text field height	9 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	Print image may vary depending on laser printer
---------	---

BMKL 15X 9 WH - Label sheet, DIN A4


0803663

<https://www.phoenixcontact.com/us/products/0803663>



Drawings

Dimensional drawing



0803663

<https://www.phoenixcontact.com/us/products/0803663>

Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

BMKL 15X 9 WH - Label sheet, DIN A4



0803663

<https://www.phoenixcontact.com/us/products/0803663>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com