

Q2-FLA16-0,75 VERB BK - Conductor connector



1403390

<https://www.phoenixcontact.com/us/products/1403390>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



QUICKON cable connector, 4-pos., connection cross section 0.34-0.75 mm², only flange with contacts of Order No. 1642140

Commercial data

Item number	1403390
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	AF6CBA
GTIN	4046356650748
Weight per piece (including packing)	7.076 g
Weight per piece (excluding packing)	7.113 g
Country of origin	DE

Q2-FLA16-0,75 VERB BK - Conductor connector



1403390

<https://www.phoenixcontact.com/us/products/1403390>

Classifications

ECLASS

ECLASS-13.0	27440113
-------------	----------

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Q2-FLA16-0,75 VERB BK - Conductor connector



1403390

<https://www.phoenixcontact.com/us/products/1403390>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com