

HC-STA-B10-HLFS-1TTP16-EL-AL - Housing



1412631

<https://www.phoenixcontact.com/us/products/1412631>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B10, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x Pg16, height: 57 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1412631
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	AF7APB
Catalog page	Page 606 (C-2-2019)
GTIN	4055626059570
Weight per piece (including packing)	155.4 g
Weight per piece (excluding packing)	147.1 g
Customs tariff number	85389099
Country of origin	PL

HC-STA-B10-HLFS-1TTP16-EL-AL - Housing



1412631

<https://www.phoenixcontact.com/us/products/1412631>

Technical data


Notes

General	for contact inserts HC-B10, BB18, DD42, M, K8/24, HV03
General	also available as a powder-coated or color version: 1372755 HC-STA-B10-HLFS-1TTP16-EL/...

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B10
No. of cable outlets	1
Type of the screw connection	1x Pg16
Type	Low design
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	44 mm
Height	57 mm
Length	73 mm

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Type of the screw connection	1x Pg16
Locking type	Pin

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)

HC-STA-B10-HLFS-1TTP16-EL-AL - Housing



1412631

<https://www.phoenixcontact.com/us/products/1412631>

	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B10-HLFS-1TTP16-EL-AL - Housing


1412631

<https://www.phoenixcontact.com/us/products/1412631>



Drawings

Dimensional drawing



Dimensional drawing


1412631


<https://www.phoenixcontact.com/us/products/1412631>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412631>

**DNV**
Approval ID: TAE000037S

**cUL Recognized**
Approval ID: E255026

**UL Recognized**
Approval ID: E255026

**EAC**
Approval ID: RU C-DE.AI30.B.01102

HC-STA-B10-HLFS-1TTP16-EL-AL - Housing



1412631

<https://www.phoenixcontact.com/us/products/1412631>

Classifications

ECLASS

ECLASS-13.0	27440202
-------------	----------

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	3.035 kg CO2e