

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable



1400295

<https://www.phoenixcontact.com/us/products/1400295>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PUR halogen-free, irradiated, orange RAL 2003, Socket angled M12, coding: A, with 3 LEDs, on Socket angled M12, coding: A, with 3 LEDs, cable length: 12 m

Commercial data

Item number	1400295
Packing unit	1 pc
Minimum order quantity	25 pc
Product key	AF1CDA
GTIN	4046356483469
Weight per piece (including packing)	492.22 g
Weight per piece (excluding packing)	222.22 g
Country of origin	PL

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable



1400295

<https://www.phoenixcontact.com/us/products/1400295>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A

Material specifications

Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU

Electrical properties

Nominal voltage U_N	24 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	3 LEDs
Status display present	yes

Connector

Connection 1

Type	Socket angled M12
Number of positions	5
Coding type	A

Connection 2

Type	Socket angled M12
Number of positions	5
Coding type	A

Cable/line

Cable length	12 m
--------------	------

PUR irradiated halogen-free orange [150]

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable



1400295

<https://www.phoenixcontact.com/us/products/1400295>

Dimensional drawing	
Number of positions	5
Shielded	no
Cable type	PUR irradiated halogen-free orange [150]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor structure, voltage supply	24x 0.15 mm
AWG power supply	20
Conductor cross section	4x 0.34 mm ² (Signal line) 1x 0.5 mm ² (PE connection)
External cable diameter	5.20 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	orange RAL 2003
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wire, color	brown, white, blue, black, green-yellow
Overall twist	5 cores, twisted
Max. conductor resistance	≤ 57.5 Ω/km (with 0.34 mm ² conductor cross-section) ≤ 39 Ω/km (with 0.5 mm ² conductor cross-section)
Nominal voltage, cable	250 V (AC)
Test voltage	2000 V (50 Hz, 5 minutes)
Smallest bending radius, fixed installation	20 mm
Smallest bending radius, movable installation	30 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 52 mm, Traversing path: 10 m, Traversing rate: 3 m/s
Halogen-free	The cable is halogen-free
Flame resistance	DIN VDE 0472 part 804, test type B
Other resistance	hydrolysis and microbe resistant UV resistant Resistant to welding splashes
Special properties	Silicone-free Irradiated
Ambient temperature (operation)	-50 °C ... 105 °C (cable, fixed installation) -40 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable



1400295

<https://www.phoenixcontact.com/us/products/1400295>

Ambient conditions

Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)
Ambient temperature (operation) (Cable, fixed installation)	-50 °C ... 105 °C (cable, fixed installation)
Ambient temperature (operation) (flexible installation)	-40 °C ... 105 °C (Cable, flexible installation)

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable




1400295

<https://www.phoenixcontact.com/us/products/1400295>


Drawings

Dimensional drawing



M12 x 1 socket, angled

Dimensional drawing




M12 x 1 socket, angled

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable

1400295


<https://www.phoenixcontact.com/us/products/1400295>

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

Schematic diagram




Pin assignment M12 socket, 5-pos., A-coded, socket side view

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable

1400295

<https://www.phoenixcontact.com/us/products/1400295>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable



1400295
<https://www.phoenixcontact.com/us/products/1400295>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

SAC-5P-M12FR3L/12-PURM12FR3LVW - Sensor/actuator cable



1400295
<https://www.phoenixcontact.com/us/products/1400295>

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com