

# EH 67,5 F-C CS/ABS GY7035 - Upper housing part



2201774

<https://www.phoenixcontact.com/us/products/2201774>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Upper housing part, flat design, no connection opening, width: 67.6 mm, height: 74.65 mm, depth: 36.95 mm, color: light gray (similar RAL 7035)

## Your advantages

- DIN rail or panel mounting for application-specific device attachment
- Easy design-in, thanks to variable housing form factor
- Complete flexibility, thanks to PCBs with horizontal, frontal, and orthogonal orientation to the front of the device
- Three cover versions for individual PCB connections
- Integration of a wide variety of PCB connection technologies for a functional device design

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2201774       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | AC12          |
| Product key                          | ACHCHC        |
| GTIN                                 | 4046356911924 |
| Weight per piece (including packing) | 32.21 g       |
| Weight per piece (excluding packing) | 32.21 g       |
| Customs tariff number                | 84879090      |
| Country of origin                    | IN            |

# EH 67,5 F-C CS/ABS GY7035 - Upper housing part



2201774

<https://www.phoenixcontact.com/us/products/2201774>

## Technical data


### Notes

|               |                                                           |
|---------------|-----------------------------------------------------------|
| Assembly note | Please observe the application note in the download area. |
|---------------|-----------------------------------------------------------|

### Product properties

|                              |                    |
|------------------------------|--------------------|
| Product type                 | Upper housing part |
| Housing type                 | DIN rail housing   |
| Housing series               | EH                 |
| Product family               | EH..F..ABS..       |
| Number (Connection openings) | 0                  |
| Ventilation openings present | yes                |

### Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 67.6 mm                                                                            |
| Height              | 74.65 mm                                                                           |
| Depth               | 36.95 mm                                                                           |

### Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color (Upper housing part)             | light gray (RAL 7035) |
| Material Upper housing part            | ABS                   |
| Flammability rating according to UL 94 | HB                    |
| Surface characteristics                | untreated             |

### Environmental and real-life conditions

#### Ambient conditions

|                                         |                                                   |
|-----------------------------------------|---------------------------------------------------|
| Max. IP code to attain                  | IP20                                              |
| Ambient temperature (operation)         | -40 °C ... 80 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                  |
| Ambient temperature (assembly)          | -5 °C ... 80 °C                                   |
| Relative humidity (storage/transport)   | 95 %                                              |

### PCB data

|                   |          |
|-------------------|----------|
| Type of PCB mount | Latching |
|-------------------|----------|

# EH 67,5 F-C CS/ABS GY7035 - Upper housing part



2201774


<https://www.phoenixcontact.com/us/products/2201774>

## Mounting

| Mounting type | Snap in |
|---------------|---------|
|---------------|---------|

## Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

# EH 67,5 F-C CS/ABS GY7035 - Upper housing part



2201774

<https://www.phoenixcontact.com/us/products/2201774>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201774>



**UL Recognized**

Approval ID: E240868

# EH 67,5 F-C CS/ABS GY7035 - Upper housing part



2201774

<https://www.phoenixcontact.com/us/products/2201774>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190603 |
| ECLASS-15.0 | 27190603 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# EH 67,5 F-C CS/ABS GY7035 - Upper housing part



2201774

<https://www.phoenixcontact.com/us/products/2201774>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)