

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB connector, number of positions: 3

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2201979       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Product key                          | ACHADB        |
| GTIN                                 | 4046356947886 |
| Weight per piece (including packing) | 6.32 g        |
| Weight per piece (excluding packing) | 6.32 g        |
| Country of origin                    | PL            |

# GMSTBT 2,5 HV/3-ST-7,25 GY X1 - PCB connector



2201979

<https://www.phoenixcontact.com/us/products/2201979>

## Technical data

### Product properties

|                     |               |
|---------------------|---------------|
| Product type        | PCB connector |
| Number of positions | 3             |

### Material specifications

|                                        |      |
|----------------------------------------|------|
| Color                                  | gray |
| Flammability rating according to UL 94 | V0   |
| Insulating material group              | I    |
| Insulating material                    | PA   |
| Contact surface material               | Sn   |

# GMSTBT 2,5 HV/3-ST-7,25 GY X1 - PCB connector



2201979

<https://www.phoenixcontact.com/us/products/2201979>

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC002638 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|