

E/ME TBUS NS35 BK - End bracket



2203310

<https://www.phoenixcontact.com/us/products/2203310>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End clamp, stable construction for DIN rail bus connector

Your advantages

- Flammability rating V0 in accordance with UL 94
- Can be mounted on the DIN rail

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2203310 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC08 |
| Product key | ACHACZ |
| GTIN | 4055626367583 |
| Weight per piece (including packing) | 14.14 g |
| Weight per piece (excluding packing) | 14.14 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

E/ME TBUS NS35 BK - End bracket



2203310

<https://www.phoenixcontact.com/us/products/2203310>

Technical data

Product properties

| | |
|----------------|-------------------|
| Product type | Mounting material |
| Housing type | DIN rail housing |
| Housing series | ME |

Dimensions

| | |
|--------|----------|
| Width | 19 mm |
| Height | 58.92 mm |
| Depth | 33.47 mm |

Material specifications

| | |
|--|------------------|
| Color (Housing) | black (RAL 9005) |
| Flammability rating according to UL 94 | V0 |
| Housing material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

E/ME TBUS NS35 BK - End bracket



2203310

<https://www.phoenixcontact.com/us/products/2203310>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250302 |
| ECLASS-15.0 | 27250302 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001041 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

E/ME TBUS NS35 BK - End bracket



2203310

<https://www.phoenixcontact.com/us/products/2203310>

Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com