

# VISU+ 2 RT UNLIMITED RED WEB3 - Visualization software



2402966

<https://www.phoenixcontact.com/us/products/2402966>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Runtime license for Visu+ including 3 web clients and redundancy function where the I/O data and variables in scripting are not limited.

## Your advantages

- Access protection with user management
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL
- Control coupling with OPC

## Commercial data

Item number	2402966
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR13
Product key	DRDAAB
GTIN	4055626175720
Weight per piece (including packing)	41.5 g
Weight per piece (excluding packing)	39.1 g
Customs tariff number	49119900
Country of origin	DE

# VISU+ 2 RT UNLIMITED RED WEB3 - Visualization software



2402966

<https://www.phoenixcontact.com/us/products/2402966>

## Technical data

### Product properties

Product type	Visualization
Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Web client capability
	Redundancy function

### System properties

Intended use for the software	Visualization
License information	
Type of license	Runtime license

Functionality	
Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Web client capability
	Redundancy function
Integrated function	Online configuration
	Password protection
	Language selection
	Web client
	Redundancy
Number of I/O nodes	128000
Number of clients	3

System requirements	
Hard disk memory	min. 1 GByte (recommended: 2 GB)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Optical drive	DVD-ROM
Screen resolution	1024 x 768 pixel(s) (XGA)

System requirements for development environment	
Operating equipment	Keyboard, mouse
Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7

# VISU+ 2 RT UNLIMITED RED WEB3 - Visualization software



2402966

<https://www.phoenixcontact.com/us/products/2402966>

	Windows® Embedded Standard 7
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003

## System requirements for runtime environment

Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® XP Embedded
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003
	Windows® CE 5.0
	Windows® CE 6.0
	Windows® Mobile

# VISU+ 2 RT UNLIMITED RED WEB3 - Visualization software



2402966

<https://www.phoenixcontact.com/us/products/2402966>

## Classifications

### ECLASS

ECLASS-13.0	27242502
ECLASS-15.0	27242502

### ETIM

ETIM 9.0	EC001416
----------	----------

### UNSPSC

UNSPSC 21.0	43231500
-------------	----------

# VISU+ 2 RT UNLIMITED RED WEB3 - Visualization software



2402966

<https://www.phoenixcontact.com/us/products/2402966>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)