

IBS OPC SERVER - Programming software



2729127

<https://www.phoenixcontact.com/us/products/2729127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS OPC server, communication interface between distributed INTERBUS and Ethernet networks and visualizations.

Commercial data

Item number	2729127
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR13
Product key	DRDBAG
GTIN	4017918163297
Weight per piece (including packing)	259.9 g
Weight per piece (excluding packing)	250.9 g
Customs tariff number	85234910
Country of origin	DE

Technical data

Product properties

Product type	Programming
Scope of supply	CD-ROM with German, English, French and Spanish product version and online documentation
Basic functions	OPC server version 2.xx support for the OPC standard functions and all optional interfaces (in accordance with OPC spec. DA 1.0a and DA 2.04)
	Networking capability (remote server)
	Simultaneous support of several controller boards
	The OPC configuration tool is integrated directly in the user interface of PC WORX and CMD and is included on the CD.
	Integrated OPC testing and diagnostics client

System properties

Intended use for the software	Driver
-------------------------------	--------

Functionality

Basic functions	OPC server version 2.xx support for the OPC standard functions and all optional interfaces (in accordance with OPC spec. DA 1.0a and DA 2.04)
	Networking capability (remote server)
	Simultaneous support of several controller boards
	The OPC configuration tool is integrated directly in the user interface of PC WORX and CMD and is included on the CD.
	Integrated OPC testing and diagnostics client
System limits	64 Ethernet connections
Associated hardware	Phoenix Contact control
Supported controllers	INTERBUS Generation 4 controller boards: Field controllers, Remote field controllers, Inline controllers, PC-based standard controllers, Factoryline controllers
Number of I/O nodes	not relevant

System requirements

Operating equipment	Keyboard, mouse
Operating system	MS Windows XP SP3, MS Windows 2000 SP4, MS Windows NT 4.0 SP6
Processor	Pentium 4/Celeron, 1 GHz
Hard disk memory	512 Mbyte
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Spanish
Optical drive	CD-ROM
Software requirements	IBS PC WORX ≥ 2.00 or IBS CMD G4 ≥ 4.5
Screen resolution	640 x 480

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com