

RBO 8-VS 3 - Connection rail



3213182

<https://www.phoenixcontact.com/us/products/3213182>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Connection rail, number of positions: 3, color: silver-colored



Your advantages

- Mounting on standard DIN rails or directly in control boxes

Commercial data

Item number	3213182
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE49
Product key	BE4Z3X
GTIN	4046356550130
Weight per piece (including packing)	29.22 g
Weight per piece (excluding packing)	29 g
Customs tariff number	85389099
Country of origin	CN

RBO 8-VS 3 - Connection rail

3213182

<https://www.phoenixcontact.com/us/products/3213182>



Technical data

Product properties

Product type	Bridge
Number of positions	3

Material specifications

Color	silver-colored
-------	----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ()
Permissible humidity (storage/transport)	30 % ... 70 %

RBO 8-VS 3 - Connection rail

3213182

<https://www.phoenixcontact.com/us/products/3213182>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RBO 8-VS 3 - Connection rail

3213182

<https://www.phoenixcontact.com/us/products/3213182>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com