

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Universal wire holding bracket, perforated, for wiring channels

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240284       |
| Packing unit                         | 200 pc        |
| Minimum order quantity               | 200 pc        |
| Sales key                            | BE74          |
| Product key                          | BE743Z        |
| GTIN                                 | 4046356478472 |
| Weight per piece (including packing) | 3.79 g        |
| Weight per piece (excluding packing) | 3.2 g         |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

## Technical data

### Product properties

|              |             |
|--------------|-------------|
| Product type | Wiring duct |
|--------------|-------------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 76.5 mm |
| Height | 20.1 mm |
| Depth  | 21.4 mm |
| Length | 20.1 mm |

### Material specifications

|            |                       |
|------------|-----------------------|
| Color      | stone gray (RAL 7030) |
| Material   | PS-HF                 |
| Components | Lead-free             |

### Cable/line

|              |     |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 90 °C |
|---------------------------------|------------------|

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

## Approvals

💡 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240284>



### VDE approval of drawings

Approval ID: 40058456

### DNV

Approval ID: TAE00004VN

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400765 |
| ECLASS-15.0 | 27400765 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001018 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31163000 |
|-------------|----------|

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)