

D-MPT 2,5-RZ - End cover

3249019

<https://www.phoenixcontact.com/us/products/3249019>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, depth: 27.1 mm, height: 36 mm, color: gray



Commercial data

Item number	3249019
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE2Z1X
GTIN	4055626429717
Weight per piece (including packing)	1.574 g
Weight per piece (excluding packing)	1.5 g
Customs tariff number	85389099
Country of origin	PL

D-MPT 2,5-RZ - End cover

3249019

<https://www.phoenixcontact.com/us/products/3249019>



Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

End cover width	2.2 mm
Height	36 mm
Depth	27.1 mm

D-MPT 2,5-RZ - End cover


3249019

<https://www.phoenixcontact.com/us/products/3249019>



Drawings

Schematic diagram




D-MPT 2,5-RZ - End cover

3249019

<https://www.phoenixcontact.com/us/products/3249019>



Schematic diagram




D-MPT 2,5-RZ - End cover

3249019

<https://www.phoenixcontact.com/us/products/3249019>



Schematic diagram



D-MPT 2,5-RZ - End cover

3249019

<https://www.phoenixcontact.com/us/products/3249019>



Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

D-MPT 2,5-RZ - End cover

3249019

<https://www.phoenixcontact.com/us/products/3249019>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.016 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com