

A/F-HA - Cover profile

1004953

<https://www.phoenixcontact.com/us/products/1004953>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealable flat cover, for covering terminal groups, with 2 red sealable plastic screws M3, suitable for all terminal blocks with M3 thread in the terminal center, dimensions: 26 x 76 mm



Commercial data

Item number	1004953
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE07
Product key	BE7121
Catalog page	Page 387 (CL-2002)
GTIN	4017918012304
Weight per piece (including packing)	4.6 g
Weight per piece (excluding packing)	4.1 g
Customs tariff number	39206100
Country of origin	DE

A/F-HA - Cover profile

1004953

<https://www.phoenixcontact.com/us/products/1004953>



Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Width	26 mm
Length	76 mm

Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V2

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

A/F-HA - Cover profile



1004953

<https://www.phoenixcontact.com/us/products/1004953>

Classifications

UNSPSC

UNSPSC 21.0	39121410
-------------	----------

A/F-HA - Cover profile



1004953
<https://www.phoenixcontact.com/us/products/1004953>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com