

HC-B 06-ANDOCK-MOD-T - Docking frame



1422076

<https://www.phoenixcontact.com/us/products/1422076>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Docking frame for two module slots, floating assembly, plastic without PE, rack compensation of ± 2.0 mm in the x/y-axis, for M4 cylinder head screws

Product description

Docking frame, fitted floating. Made from plastic without PE. Slide-in offset x/y axis ± 2.0 mm

Commercial data

Item number	1422076
Packing unit	2 pc
Minimum order quantity	2 pc
Product key	AF7ACZ
Catalog page	Page 585 (C-2-2017)
GTIN	4055626290089
Weight per piece (including packing)	1.695 g
Weight per piece (excluding packing)	1.695 g
Country of origin	DE

HC-B 06-ANDOCK-MOD-T - Docking frame



1422076

<https://www.phoenixcontact.com/us/products/1422076>

Technical data

Product properties

Product type	Docking frame
Type	B6
Number of module slots	2

Material specifications

Material	PC
Flammability rating according to UL 94	V0

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mounting

Assembly note	Due to the plastic frame without PE, a metal attachment panel must be grounded separately.
	Floating fixing with special washer (Item No. 1587496) and standard M4 screws/nuts, screw length: 6 mm + panel thickness + (locking nut in the case of panel without thread). 2 mm play.

HC-B 06-ANDOCK-MOD-T - Docking frame




1422076

<https://www.phoenixcontact.com/us/products/1422076>


Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Mounting cutout

HC-B 06-ANDOCK-MOD-T - Docking frame



1422076
<https://www.phoenixcontact.com/us/products/1422076>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com