

NBC-HDMI-HAM/1,5-PVC/HAM - HDMI cable



1332081

<https://www.phoenixcontact.com/us/products/1332081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HDMI cable, degree of protection: IP20, cable length: 1.5 m, number of positions: 19, material: LCP, HDMI High Speed

Your advantages

- HDMI high-speed patch cables
- Integrated network transmission thanks to HDMI Ethernet channel
- Reliable transmission of 4K videos

Commercial data

Item number	1332081
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB14
Product key	ABNEBA
GTIN	4063151628970
Weight per piece (including packing)	100.7 g
Weight per piece (excluding packing)	100.7 g
Customs tariff number	85444290
Country of origin	CN

NBC-HDMI-HAM/1,5-PVC/HAM - HDMI cable



1332081

<https://www.phoenixcontact.com/us/products/1332081>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	HDMI High Speed
Number of positions	19
Shielded	yes

Electrical properties

Insulation resistance	100 M Ω
Test voltage	500 V AC
Test voltage Core/Core	500 V AC
Test voltage Core/Shield	500.00 V AC
Wave impedance	100 Ω

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 10000
-----------------------------	---------

Material specifications

Color of the housing part	black
Flammability rating according to UL 94	UL94 V0
Housing material	LCP

Dimensions

Width	20.3 mm
Height	12 mm
Length	49.3 mm

Connector

Connection 1

Type	Plug straight HDMI type A
Shielded	yes
Insertion/withdrawal cycles	> 10000
Insulation resistance	100 M Ω
Degree of protection	IP20

Connection 2

Type	Plug straight HDMI type A
Degree of protection	IP20

Cable/line

Cable length	1.50 m
--------------	--------

NBC-HDMI-HAM/1,5-PVC/HAM - HDMI cable



1332081

<https://www.phoenixcontact.com/us/products/1332081>

PVC HDMI high speed black [HDMI]

Shielded	yes
UL AWM Style	20276
Cable type	PVC HDMI high speed black
Cable type (abbreviation)	HDMI
External cable diameter	6.00 mm
Outer sheath, material	PVC
External sheath, color	black
Shielding	Aluminum-lined foil

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

NBC-HDMI-HAM/1,5-PVC/HAM - HDMI cable



1332081

<https://www.phoenixcontact.com/us/products/1332081>

Classifications

ECLASS

ECLASS-13.0	27060307
-------------	----------

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

NBC-HDMI-HAM/1,5-PVC/HAM - HDMI cable



1332081

<https://www.phoenixcontact.com/us/products/1332081>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com